


Application examples



- 3 Type**
- A1** Through-hole
 - A2** Through-hole with continuous thread
 - A3** Through-hole with thread on both sides

d ₁	Length l ±0,1				Length l ±0,2			d ₂ Through-hole for screw	d ₃ Thread	d ₄	d ₅	t min.
	Type A1		Type A2	Type A3	Type A1	Type A2	Type A3					
22	10	12	16	20	30	50	M 5	M 6	18	22,8	12	
28	12	16	20	30	50	75	M 6	M 8	24	28,8	16	
34	12	16	20	30	50	100	M 8	M 10	30	34,8	20	

Specification

Spacers	
Stainless steel AISI 316L	
Matte finish (Ra < 0.8 µm)	MT
Sealing ring	
• HNBR	H
• EPDM	E
• FKM	F
• FDA compliant material	
• Blue	
• Hardness 85 ±5 Shore A	

RoHS

Technical Information	Page
Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Spacers GN 6226 are intended for use in hygienic areas. The versions with sealing ring H and E comply additionally according to the guidelines of the EHEDG and DGUV Test guidelines. The sealed mounting surfaces enable fastening without dead spaces. The high quality finish prevents adherence of dirt and facilitates cleaning.

Spacers are used to fasten parts at an offset parallel to their plane of installation. This avoids doubling up on surfaces and leaves space for cleaning. The internal thread can alternatively be used as a through hole by a screw with a smaller thread.

see also...	Page
GN 1580 Screws (Hygienic Design)	QVX
GN 1580 Nuts (Hygienic Design)	QVX
GN 1581 Screws (Low-Profile Head, Hygienic Design)	QVX
GN 1582 Screws (with Recessed Stud for Loss Protection, Hygienic Design)	QVX

Accessory	
GN 7600 Sealing Rings	QVX

How to order

1	d ₁
2	Length l
3	Type
4	Finish
5	Material (Sealing ring)

GN6226-28-75-A3-MT-H