




d ₁	d ₂		h		Length l	
	MS	KLG	MS	KLG	MS	KLG
M 12 x 1,5	14	15	7,5	8	5	6
M 16 x 1,5	18	20	8	9	5	6
M 20 x 1,5	22	24	8,5	9,5	6	6
M 25 x 1,5	28	29,7	11	11,5	7	8
M 32 x 1,5	35	37,1	12	12	8	8
M 40 x 1,5	44	46	13	13	8	8
M 50 x 1,5	54	56,3	15	15	9	10
M 63 x 1,5	67	69,3	16	17	10	12

Specification

Threaded plug

- Brass MS
- Nickel-plated
- Operating temperature -20 °C to +80 °C
- Plastic, polyamide (PA) KLG
- Glass fiber reinforced
- Operating temperature -40 °C to +100 °C
- Gray, RAL 7035

O-ring for MS

Acrylonitrile butadiene rubber (NBR)

Protection class

- IP 68 for MS
- IP 54 for KLG

RoHS

Threaded plugs GN 62444.2 seal unused mounting holes for cable glands. They can be screwed into an existing internal thread or mounted in a through hole using a mounting nut. The metal versions include an O-ring for sealing against the enclosure. The plastic version is sealed without an additional sealing ring.

see also...	Page
GN 62444.2 Threaded Plugs (PG Thread)	QVX
GN 62444 Cable Glands (Metric Thread)	QVX
GN 62444.3 Multiple Sealing Inserts	QVX
GN 62444.4 Reducers (Metric Thread)	QVX

Technical Information

IP Protection Classes	QVX
Plastic Characteristics	QVX

Accessory

GN 62444.1 Mounting Nuts	QVX
--------------------------	-----

How to order		1	d ₁
GN 62444.2-M50x1,5-MS		2	Material