



ROSTFREI  
Inox  
Stainless  
Steel

| 2              |                | 3          |    | 4  |    |    |    |    |    |                |                |                |                |
|----------------|----------------|------------|----|----|----|----|----|----|----|----------------|----------------|----------------|----------------|
| d <sub>1</sub> | d <sub>2</sub> | Length l ≈ |    |    |    |    |    |    |    | d <sub>3</sub> | h <sub>1</sub> | h <sub>2</sub> | h <sub>3</sub> |
| 32             | M 6            | 16         | 20 | 25 | 30 | 35 | 45 | -  | -  | 12             | 20             | 10             | 9              |
| 40             | M 8            | 16         | 20 | 25 | 30 | 35 | 40 | 45 | 55 | 14             | 25             | 13             | 10             |
| 50             | M 10           | 25         | 30 | 35 | 45 | 55 | -  | -  | -  | 18             | 32             | 20             | 12             |
| 63             | M 12           | 30         | 35 | 40 | 50 | 60 | -  | -  | -  | 20             | 40             | 25             | 14             |

Specification

- Knob

Technopolymer (Polyamide PA)

- Shock-resistant

- Black matte finish
- GN 6335.4

Threaded stud

Steel

Zinc plated, blue passivated
- GN 6335.5

Threaded stud

Stainless steel AISI 303
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

1

Information

The hand knobs have an immaculate contact or clamping surface thanks to the protruding steel / stainless steel bushing.

see also...

- Hand Knobs 6335.4

(without Protruding Bushing, Threaded Stud Steel) → Page 587
- Hand Knobs 6335.5

(without Protruding Bushing, Threaded Stud Stainless Steel) → Page 587

| How to order (Threaded stud steel) |  | 1 | Material       |
|------------------------------------|--|---|----------------|
|                                    |  | 2 | d <sub>1</sub> |
|                                    |  | 3 | d <sub>2</sub> |
|                                    |  | 4 | Length l       |

| How to order (Threaded stud stainless steel) |  | 1 | Material       |
|----------------------------------------------|--|---|----------------|
|                                              |  | 2 | d <sub>1</sub> |
|                                              |  | 3 | d <sub>2</sub> |
|                                              |  | 4 | Length l       |