



Rostfrei
Inox
Stainless
Steel

4 Type

- A** Without bore (unmachined)
- B** With through bore H7
- C** With blind bore H7
- D** With threaded through bore
- E** With threaded blind bore

2			3		3							
d ₁	GG		d ₂	d ₃ H7 Bore	d ₄	h ₁	h ₂	h ₃	h ₄	t ₁	t ₂	
	NI	AL	Thread Type D Type E	Type B Type C		Type B, C, D, E	Type B, C, D, E	Type A	Type A	min.		
-	-	20	M 4	-	8	13	7	14	8	8	7	
-	-	25	M 5	-	10	16	9	17	10	10	8	
32	32	32	M 6	B 6	12	20	9	21	10	12	10	
40	40	40	M 8	B 8	14	25	13	26	14	15	13	
50	50	50	M 10	B 10	18	32	18	34	20	18	16	
63	63	63	M 12	B 12	20	40	23	42	25	22	20	
80	-	80	M 16	B 16	25	50	28	52	30	28	20	
100*	-	-	M 20	B 20	32	63	36	65	38	36	25	

* not available in version ZB

Specification

- Cast iron **GG**
 - Fettle and tumbled
 - Zinc plated, blue passivated
 - Thread: screw mobility (Type D and E)
- Stainless steel **NI**
 - Precision casting AISI CF-8
 - Matte shot-blasted (Type A, D, E)
- Aluminum **AL**
 - Forged (Type A, C, D, E)
 - Matte finish (tumbled)
 - Flash mark not visible
 - Polished

• RoHS

On request

- Powder coated

Information

see also...

- Hand Knobs DIN 6335 (Plastic) → Page 586
- Hand Knobs GN 6335.1 (Duroplast, with Protruding Steel Bushing) → Page 588
- Hand Knobs GN 6335.2 (Technopolymer, with Protruding Steel Bushing) → Page 588
- Hand Knobs DIN 6335 with Loss Protection GN 111.7 → Page 2084

How to order (Without bore, matte)	1 Material
DIN 6335-AL-63-A	2 d ₁
	4 Type

How to order (Cast iron)	1 Material
DIN 6335-GG-63-M12-D	2 d ₁
	3 d ₂ (d ₃)
	4 Type

How to order (Aluminum)	1 Material
DIN 6335-AL-50-B10-C-MT	2 d ₁
	3 d ₃ (d ₂)
	4 Type
	5 Finish