




1 d₀	2 d₁ Bore	3 Number of holes			d₂	h	For cable gland
8	2	3	4	-	10,6	7,5	GN 62444-...-8-...
8	3	2	4	-	10,6	7,5	GN 62444-...-8-...
10	4	2	3	-	13,3	8,5	GN 62444-...-10-...
10	5	2	3	-	13,3	8,5	GN 62444-...-10-...
12	4	3	-	-	15,3	8,5	GN 62444-...-12-...
12	5	2	3	-	15,3	8,5	GN 62444-...-12-...
12	6	2	-	-	15,3	8,5	GN 62444-...-12-...
14	4	2	3	5	17,4	9	GN 62444-...-14-...
14	5	4	-	-	17,4	9	GN 62444-...-14-...
14	6	2	3	4	17,4	9	GN 62444-...-14-...
17	6	2	3	-	19,8	9,3	GN 62444-...-17-...
17	8	2	-	-	19,8	9,3	GN 62444-...-17-...
18	5	4	-	-	22,2	11	GN 62444-...-18-...
18	7	2	3	4	22,2	11	GN 62444-...-18-...
18	8	2	3	-	22,2	11	GN 62444-...-18-...
18	9	2	-	-	22,2	11	GN 62444-...-18-...
21	6	6	-	-	25,1	12,5	GN 62444-...-21-...
21	7	4	-	-	25,1	12,5	GN 62444-...-21-...
21	8	4	-	-	25,1	12,5	GN 62444-...-21-...
25	5	8	-	-	29,8	13	GN 62444-...-25-...
25	8,5	5	-	-	29,8	13	GN 62444-...-25-...

Specification

Plastic

Thermoplastic elastomer

• Operating temperature -30 °C to +100 °C

• Black

RoHS

Technical Information

Plastic Characteristics

4

TPE

Page

QVX

Multiple sealing inserts GN 62444.3 replace the simple seal inserts supplied with cable glands. This allows multiple cables or wires to be fed through a single cable gland, strain-relieved, and sealed.

see also...

GN 62444 Cable Glands (Metric Thread)

GN 62444 Cable Glands (PG thread)

GN 62444 Cable Glands (NPT thread)

Page

QVX

QVX

QVX

How to order

1

d₀

2

d₁

3

Number of holes

4

Material

GN62444.3-17-6-3-TPE