



**3 Type**

- E** With threaded blind bore
- C** With plain blind bore, Tol. H7

d <sub>1</sub>	d <sub>2</sub>			d <sub>3</sub> H7		d <sub>4</sub>	h <sub>1</sub>		h <sub>2</sub>		h <sub>3</sub>	t min.
	GN 6336.1	GN 6336.2	Thread (Type E)	Bushing steel	Bushing Stainless steel		GN 6336.1	GN 6336.2	GN 6336.1	GN 6336.2		
25*	M 5	-	M 5	-	-	10	-	16	-	8	6	9,5
32	M 6	-	M 6	B 6	-	12	21	20	10	10	8,5	12
40	M 6	M 8	M 8	B 6	B 8	14	26	26	13	13	10	14
50	M 8	M 10	M 10	B 8	B 10	18	34	32	17	17	10	18
63	M 10	M 12	M 12	B 10	B 12	20	42	40	21	21	14	22
80	M 12	M 16	M 16	B 16	-	25	52	52	25	27	15	30

\* only available for GN 6336.2

**Specification**

- **GN 6336.1**  
Plastic  
Duroplast (PF)  
Black, shiny finish  
Bushing  
- Steel  
- Zinc plated, blue passivated  
- Stainless steel AISI 303
- **GN 6336.2**  
Plastic  
Technopolymer (Polyamide PA)  
- Shock-resistant  
- Black, matte finish  
Bushing  
- Steel  
- Zinc plated, blue passivated  
- Stainless steel AISI 303
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

**4 Information**

Star knobs GN 6336.1 / GN 6336.2 with protruding bushing have important advantages:

The face of the bushing is exactly square to the bore and is with the complete diameter out of steel or Stainless Steel. The protruding steel bushing allows a perfect cross-dowels connection.

see also...

- Star Knobs GN 6336 (Cast Iron / Stainless Steel / Aluminum) → Page 540
- Star Knobs DIN 6336 (Plastic, without Protruding Bushing) → Page 544

How to order (Duroplast, bushing stainless steel)	1 d <sub>1</sub>
	2 d <sub>2</sub> (d <sub>3</sub> )
	3 Type
	4 Material bushing

How to order (Technopolymer, bushing steel)	1 d <sub>1</sub>
	2 d <sub>3</sub> (d <sub>2</sub> )
	3 Type