



elesa
Original design EBP.SAN



3 Type
B Mounting from the operator's side

¹ l ₁	² d ₁	d ₂	h ₁	h ₂	l ₂	l ₃ min.	s	A/F	t
117 ±0,5	8,5	26	39	18	143	91	8,5	13	8,5
179 ±1	8,5	29	51	19	208	150	9,5	13	16

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black-gray, RAL 7021, matte finish
- White, RAL 9016, matte finish



WSA

Cover cap

- Plastic, Polyamide (PA)
- Black-gray (for SGA)
- White (for WSA)

RoHS

Cabinet U-handles GN 628.1 are manufactured from an antimicrobial plastic. Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilising at temperatures below 130 °C will also have no effect on the antimicrobial property.

With these properties, the handles are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...

GN 628 Cabinet U-Handles (Mounting from the operator's side or back) **Page** QVX

Technical Information

Product Family Sanline	QVX
Product Family Ergostyle®	QVX
Strength Properties	QVX
Plastic Characteristics	QVX

Accessory

GN 628.2 Distance Bushings **Page** QVX

How to order		¹ l ₁
		² d ₁
GN 628.1-117-8,5-B-SGA		³ Type
		⁴ Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

