



- 4 Type**
- M** Straight lever
 - N** Angled lever

- 1**
- 2**
- 3**

d ₁	d ₂	l ₁	d ₃	d ₄	h ₁	h ₂	h ₃ ≈	l ₂	l ₃ ≈					
20	M 8	20	25	32	40	50	63	13,5	20	25	8	46	74	70
25	M 10	20	25	32	40	50	63	16	25	29	8	58	93	87
28	M 12	25	32	40	50	63	80	19	30	33,5	10,5	70,5	116	109

Specification

- Steel
Blackened
Threaded stud
Property class 5.8
- Ball knobs DIN 319
Plastic, Duroplast
Black, shiny finish
- *Strength Values of Screws* → Page 2152
- RoHS

Information

Adjustable clamping levers GN 6337.3 have proved to be ideal whenever parts have to be clamped in a confined space or a particular lever position is required. The insert is connected by the lever via serrations in the ball bore which can be disengaged.

Pushing the lever down, disengages the serrations and the lever can be swivelled to the ideal clamping position. Engagement is achieved by releasing the lever.

Should a rotation of 360° not be possible, the insert can be lightly screwed in (after the lever is disengaged) via a slot in the knurled screw.

How to order		1	d ₁
		2	d ₂
		3	l ₁
		4	Type
GN 6337.3-28-M12-50-N			

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

