



d <sub>1</sub>	d <sub>2</sub>	s	For screws with thread
6,4	17	3	M 6
8,4	23	4	M 8
10,5	28	4	M 10
13	35	5	M 12
15	40	5	M 14
17	45	6	M 16
21	50	6	M 20
25	60	8	M 24
31	68	10	M 30

### Specification

- Heat-treated steel
  - Tempered  
Hardness (350 + 80) HV 30
  - Phosphate-treated
  - Blanked
  - Not deburred
- RoHS

### Information

Washers DIN 6340 are mainly used for elongated holes.  
Size 15 is not on the official DIN standard sheet.

see also...

- *Heavy Duty Washers GN 6339* → Page 1088

How to order

**DIN 6340-17**

1 d<sub>1</sub>