



elesa
Original design ESP.



2 Type

- A** Mounting with hex head screw
- B** Mounting with countersunk screw

1

l_1	b_1	b_2	d	h_1	h_2	h_3	h_4	$l_2 \pm 0,5$	l_3	t
114	35	19	6,5	33	7	11	9	93,5	74	5

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +110 °C
- Black-gray, matte finish, similar to RAL 7021

Cover

- Plastic, Polyamide (PA)
- Black-gray, RAL 7021, shiny finish
- Orange, RAL 2004, shiny finish
- Gray, RAL 7035, shiny finish
- Yellow, RAL 1021, shiny finish
- Blue, RAL 5024, shiny finish
- Red, RAL 3000, shiny finish
- Green, RAL 6017, shiny finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

RoHS

The design of ledge handles GN 630 matches the product family of the Ergostyle®.

A typical application for ledge handles GN 630 is on double swing doors on machine shrouds or fixtures.

The cover offers protection for the operator's fingers. At the same time it also covers the two fixing screws.

The cover is supplied loose.

see also...

	Page
GN 630.1 Cabinet U-Handles (Plastic)	QVX

Technical Information

Product Family Ergostyle®	QVX
Strength Properties	QVX
Plastic Characteristics	QVX

How to order

GN 630-114-B-DOR

1	l_1
2	Type
3	Color of the cover