



1

2

d ₁	Length l - Thread length b ₁				b ₂	d ₂
	l - b ₁	l - b ₁	l - b ₁	l - b ₁		
M 6	50 - 30	80 - 50	-	-	9	5,3
M 8	40 - 20	63 - 40	100 - 63	-	11	7,1
M 10	50 - 25	80 - 50	125 - 75	200 - 125	13	9
M 12	50 - 25	80 - 50	125 - 75	200 - 125	15	10,7
M 14	63 - 32	100 - 63	160 - 100	250 - 160	17	12,6
M 16	63 - 32	100 - 63	160 - 100	250 - 160	19	14,6
M 20	80 - 32	125 - 70	200 - 125	315 - 190	27	18,2
M 24	100 - 50	160 - 100	250 - 160	400 - 250	35	21,9

Specification

- Heat-treated steel
 - M 6 ... M12: Property class 10.9
 - M14 ... M24: Property class 8.8
 - Blackened
- *Strength Values of Screws* → Page 2152
- RoHS

Information

Studs DIN 6379 are primarily used with T-nuts DIN 508.

Complete clamping screws can be created by combining them with hexagon nuts DIN 6330 and washers DIN 6340.

The official DIN standard sheet also specifies a version with longer thread b₂ as well as thread M30 and M36; however, size M14 is not included.

see also...

- *T-Nuts DIN 508* → Page 1162

How to order

DIN 6379-M12-125

1 d₁

2 Length l