



Type A : without stop




Type B : with stop




**elesa**  
Original design RLT-B

**Type**

- A Without stop
- B With stop



Mounting on top of the roller track



Mounting on the bottom side of the roller track (only possible for type A)

**Specification**

- Plastic
- Polyamide (PA)
- Black
- Temperature resistant up to 90 °C
- *Plastic Characteristics* → Page 2158
- RoHS

**Information**

Brakes GN 646.5 will reduce the speed of the material conveyed, disrupt or stop the transporting altogether. They are mounted by snapping them into the roller track.

In type A (without stop), the brakes can also be mounted on the bottom side of the roller track. This, however, works only for roller tracks GN 646.1 made of polyurethane (TPU).

see also...

- *Roller Tracks GN 646.1* → Page 2009

How to order

**GN 646.5-A**

1 Type

