




Type K

Identification no. 1

Identification no. 2



elesa

Original design GLB-1 / GLB-2



Inox  
Stainless  
Steel



1 Type

- K Ball-shaped rollers
- Z Cylindrical rollers
- ZA Cylindrically offset rollers




2 Identification no.

- 1 Single row
- 2 Double row

Type Z



Type ZA




3

l <sub>1</sub>	b <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>		h <sub>2</sub>	h <sub>3</sub>	l <sub>2</sub>
							Id. no. 1	Id. no. 2			
375	31,2	30,6	31,75	12,5	11,25	13,5	44	79,8	71,8	35,5	75

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10





**Specification**



**Carrier profile segment**

Plastic, polyacetal **POM**  
Black

**Rollers**

Plastic, polyethylene (PE)  
• Operating temperature -20 °C to 90 °C  
• Gray **GR**

**Axis**

Stainless steel AISI 304

RoHS

**Accessory**

**Page**

GN 6473.1 Retaining Profiles	QVX
GN 6473.2 Connecting Elements	QVX

Side guide segments GN 6473 are attached to the sides of conveyor sections, and their rollers guide the conveyed goods without damage. Due to their segmentation, they are particularly suited for use on curves.

The type of rollers used depends on the conveyed material. Type K is used for cans and plastic boxes. For cardboard boxes, type Z can be used for an even material flow. For containers of glass, type ZA is used since it allows easy removal of any contamination due to glass breakage.

Fastening is carried out with retaining profiles GN 6473.1, which are attached to conveyor systems with connecting elements GN 6473.2. Included are 5 segments with total length  $l_1$ .

**see also...**

**Page**

GN 6471 Side Guides	QVX
GN 6472 Side Guides	QVX

**Technical Information**

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

**How to order**

<b>1</b>	Type
<b>2</b>	Identification no.
<b>3</b>	$l_1$
<b>4</b>	Material
<b>5</b>	Color

**GN6473-Z-2-375-POM-GR**