



**4 Type**  
K With threaded bushing

d <sub>1</sub>	d <sub>2</sub>				d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.	
	Plastic KU Steel bushing	Plastic KU MS bushing	Plastic KU NI bushing	Plastic KT Steel bushing				Steel bushing MS bushing	NI bushing
20	-	M 4	-	-	10	13	6	7	-
25	M 5	M 5	M 5	-	13	17	8	9,5	7,5
32	M 6	M 6	M 6	M 6	14	20	10	12	9
40	M 8	M 8	M 8	M 8	18	25	13	14	12
50	M 10	M 10	M 10	M 10	22	32	20	18	15
63	M 12	M 12	M 12	M 12	26	40	25	22	18
80	M 16	M 16	M 16	M 16	35	50	30	30	24
100	M 20	-	-	-	34	65	38	30	-

**Specification**

- Plastic Duroplast (PF) **KU**  
Black, shiny finish  
Bushing  
- Steel, zinc plated, blue passivated —  
- Brass **MS**  
- Stainless steel AISI 304 **NI**
- Plastic Technopolymer (Polyamide PA) **KT**  
- Shock-resistant  
- Black, matte finish  
Bushing  
Steel zinc plated, blue passivated
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

**Information**

Hand knobs DIN 6335 with bore H7 are available as GN 6335.1 / GN 6335.2. The size 100 is not on the official DIN standard sheet.

see also...

- Hand Knobs GN 6335.1 / GN 6335.2 (with Protruding Bushing Steel) → Page 588
- Hand Knobs DIN 6335 with Loss Protecting GN 111.7 → Page 2084

How to order (Duroplast, bushing steel)

1	Material
2	d <sub>1</sub>
3	d <sub>2</sub>
4	Type

**DIN 6335-KU-63-M12-K**

How to order (Duroplast, bushing stainless steel)

1	Material
2	d <sub>1</sub>
3	d <sub>2</sub>
4	Type
5	Bushing

**DIN 6335-KU-50-M10-K-NI**