



d <sub>1</sub>	l <sub>1</sub> ±1							a	b	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub> max.	l <sub>6</sub>
20	180	200	250	300	350	400	-	48	28	M 8	45	58	19	10	25	6	9,5
30	300	350	400	500	600	700	1000	57	38	M 10	60	78	23	12	35	9	14,5

**Specification**

**Handle tube**

Wall thickness 1,5 mm

- Aluminum
  - Powder coated
    - Black, RAL 9005, textured finish
  - Anodized, natural color
- Stainless steel AISI 304 ground, matte shiny

- SW
- EL
- NG

**End pieces**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature up to 100 °C
- Black, matte finish

**Fastening set**

- Stainless steel AISI 304
- Socket cap screws ISO 4762
- Hex nuts ISO 4032
- Washers DIN 125

RoHS

The handle tube of the cabinet U-handles GN 667 can be mounted without any further machining, allowing special lengths to be realised easily. For handles with longer spans or greater loads, supports are available on request.

see also...

	Page
<b>GN 767</b> Cabinet U-Handles (Handle Tube Powder Coated)	QVX
<b>GN 767.1</b> Cabinet U-Handles (Handle Tube Anodized)	QVX
<b>GN 667.2</b> Cabinet U-Handles (Mounting from the Back)	QVX

**Technical Information**

Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Handle tube, aluminum)

1	d <sub>1</sub>
2	l <sub>1</sub>
3	Finish

**GN 667-20-200-EL**

How to order (Handle tube, stainless steel)

1	d <sub>1</sub>
2	l <sub>1</sub>
3	Finish

**GN 667-30-1000-NG**