



elesa
Original design EKK.



¹ d ₁	² d ₂		d ₃	h ₁	h ₂	t min.
16	M 3	-	8,5	13	8,5	6
18	M 4	-	10,5	15,5	10,5	6
21	M 4	M 5	12,5	18	10,5	10
25	M 6	M 8	14,5	22,5	14	12
31	M 6	M 8	18,5	27	17	15
31	M 10	-	18,5	27	17	17
35	M 6	M 8	20	27,5	17	15
35	M 10	-	20	27,5	17	17

Specification

Knob

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Color
 - Black-gray, RAL 7021, matte finish
 - Red, RAL 3000, matte finish
 - Orange, RAL 2004, matte finish
 - Gray, RAL 7035, matte finish
 - Yellow, RAL 1021, matte finish
 - Blue, RAL 5024, matte finish
 - Green, RAL 6017, matte finish

- **SG**
- **RT**
- **OR**
- **GR**
- **GB**
- **BL**
- **GN**

Threaded bushing

Brass

RoHS

The design of the GN 676 knurled knobs matches the product family Ergo-style®.

These knurled knobs are used for manual applications for clamping or pulling. The concave top of the nut is a comfortable rest point for the thumb during a pulling application.

The knurled section makes the knobs easier to install and also allows them to be used as knurled nuts.

see also...

	Page
GN 676.1 Knobs (Steel, blackened)	QVX
GN 676.5 Knobs (Stainless Steel)	QVX
GN 76 Mushroom Shaped Knobs (Phenolic resin)	QVX
GN 676 Knurled Knob Screws	QVX

Technical Information

Product Family Ergostyle®	QVX
Plastic Characteristics	QVX

How to order

GN 676-25-M6-RT

¹ d ₁	
² d ₂	
³ Farbe	

