



1		2		3			4						
d ₁	d ₂	l ₁	l ₂	l ₃	l ₄	d ₃	d ₄	d ₅ +0,05	h ₁	h ₂	l ₂	l ₃	l ₄
32	M 6	25	35	45	-	15	14	4,5	20	10	5,1	3,6	7,6
40	M 8	30	40	50	60	18	18	6,1	25	13	6,2	4,2	9,2
40	M 8	30	40	50	60	21	18	6,1	25	13	6,2	5	10
40	M 8	30	40	50	60	25	18	6,1	25	13	6,2	5,5	10,5
40	M 8	30	40	50	60	32	18	6,1	25	13	6,2	6	11
40	M 8	30	40	50	60	40	18	6,1	25	13	6,2	8	13
50	M 10	35	45	55	65	21	22	7,8	32	17	7,3	4,3	10
50	M 10	35	45	55	65	25	22	7,8	32	17	7,3	4,6	10,5
50	M 10	35	45	55	65	32	22	7,8	32	17	7,3	5	11
50	M 10	35	45	55	65	40	22	7,8	32	17	7,3	7	13
63	M 12	40	60	80	-	25	26	9,4	40	21	8,3	3,6	10,5
63	M 12	40	60	80	-	32	26	9,4	40	21	8,3	4,2	11
63	M 12	40	60	80	-	40	26	9,4	40	21	8,3	6,2	13
63	M 12	40	60	80	-	50	26	9,4	40	21	8,3	8,7	15,5

Specification

- Star knob DIN 6336
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Threaded stud
Stainless steel AISI 304 Cu
- Thrust pad
Plastic
Technopolymer (Polyacetal POM)
- Temperature resistant up to 80 °C
- Black, matte finish
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Star knobs GN 6336.11 / GN 6336.12 have a ball pin whose diameter is smaller than the core diameter of the thread.

The movable thrust pad is easily clipped on and taken off.

The thrust pads are supplied disassembled.

see also...

- Knurled Screws GN 421.12 (with Movable Thrust Pad) → Page 639
- Star Knobs with Threaded Stud GN 6336.11 / GN 6311.12 with Loss Protection GN 111.7 → Page 2084

How to order (With ball pin)	
1	d ₁
2	d ₂
3	l ₁
GN 6336.11-40-M8-50	

How to order (With movable thrust pad)	
1	d ₁
2	d ₂
3	l ₁
4	d ₃
GN 6336.12-50-M10-45-25	