



d ₁	d ₂	Length l ≈												d ₃	h ₁	h ₂
		Material ST						Material SK								
25	M 5	10	15	20	25	30	-	-	10	15	20	25	-	12	16	8
25	M 6	10	16	20	25	30	-	-	-	-	-	-	-	12	16	8
32	M 6	10	16	20	25	30	-	-	10	16	20	25	30	14	20	10
32	M 8	20	25	30	40	50	60	-	-	-	-	-	-	14	20	10
40	M 8	20	25	30	40	50	60	-	20	25	30	40	-	18	25	13
40	M 10	20	25	30	45	50	55	60	-	-	-	-	-	18	25	13
50	M 10	20	25	30	45	50	55	60	20	25	30	45	55	22	32	17
50	M 12	30	40	50	60	-	-	-	-	-	-	-	-	22	32	17
63	M 12	30	40	50	60	-	-	-	30	40	50	-	-	26	40	21

Specification

- Knob
Technopolymer (Polyamide PA) **ST**
Shock-resistant, black matte finish
Threaded stud
Stainless steel
M5...M10: AISI 304 Cu
M12: AISI 303
- Knob **SK**
Duroplast (PF)
Black shiny finish
Threaded stud
Stainless steel
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**



Information

- Star knobs GN 6336.5 comply with DIN 6336 type L.
- see also...**
- *Star Knobs GN 6336.10 (with Brass / Plastic Pivot)* → Page 548
 - *Star Knobs GN 6336.12 (with Movable Thrust Pad)* → Page 549
 - *Star Knobs GN 6336.13 (with Loss Protection)* → Page 551
 - *Star Knobs GN 6336.5 with Loss Protection GN 111.7* → Page QVX

How to order

1	Material
2	d₁
3	d₂
4	Length l

GN 6336.5-ST-63-M12-60

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

