


Application example
Type B



ROSTFREI
Inox
Stainless
Steel

2 Type

- A** Flat, without stop edge
- B** Flat, with stop edge

1

Steel							
d ₁	Type A	Type B	d ₂ +1	d ₃ +1	h ±0,5	Length l	s
12 ±0,1	-	-	3,5	6,5	-	-	2
17 ±0,1	-	-	5,5	8,5	-	-	2
27 ±0,2	27 ±0,2	27 ±0,2	5,5	11	8	21	3
34 +0,2/+0,8	34 +0,2/+0,8	34 +0,2/+0,8	5,5	11	8	29	3
45 +0,1/+0,5	45 +0,1/+0,5	45 +0,1/+0,5	5,5	11	8	39	3
64 ±0,3	64 ±0,3	64 ±0,3	5,5	11	8	58	3

1

Stainless steel							
d ₁ ±0,2	Type A		d ₂ +1	d ₃ +1	h ±0,5	Length l	s
27	-	-	5,5	11	-	-	3
45	-	-	5,5	8,5	-	-	2

Specification

- Steel
Zinc plated
- Stainless steel
Magnetic
- RoHS

3

Information

ST

Holding discs GN 70 are used as companion parts for retaining magnets when they are used in connection with non-magnetic materials.

NI

Type B prevents the magnet from sliding since the magnetic forces are generally larger than the achievable lateral forces arising due to the friction partners present.

They can be fixed with countersunk screws (e.g. DIN 7991), but also with any commercial wood or sheet metal countersunk screws.

see also...

- Rubber Caps GN 70.2 → Page 2074

How to order

GN 70-27-A-NI

- 1** d₁
- 2** Type
- 3** Material