Type **A**



Type **B**





STAINLESS ★ STAINLESS ★★★★

4 Form

A With cylindrical bore
B With bore for countersunk screw

2 d_1 $^{+0,5}_{+0,2}$	3 d_2		d_3	s
3	8	10	6,3	2
4	10	13	8,4	2,5
5	13	16	10,5	3
6	15	20	12,6	4
8	20	26	16,8	5
10	25	32	21	6,5
12	30	40	25,2	7,5
16	40	55	31,5	9

Specification	1	5
Steel	**ST**	
• Turned		
• Blackened		**BT**
• Zinc plated, blue passivated		**ZB**
• Case-hardened, blackened		**H**
Stainless steel AISI 303	**NI**	
Turned, matte shot blasted		**MT**
Stainless steel AISI 316L	**A4**	
Turned, plain		**MT**

RoHS

Washers GN 6341 are used mainly in mechanical machine and jig construction when washers DIN 125, DIN 9021 and DIN 6340 no longer meet requirements.
In particular, the version for countersunk screw (Type B) is ideal for solid screw connections with a low construction height.

see also...	Page
GN 6339 Heavy Duty Washers (Steel)	QVX
GN 184 Countersunk Washers (Steel)	QVX
GN 184.5 Countersunk Washers (Stainless Steel)	QVX
DIN 6340 Washers (Steel)	QVX

Technical Information

Stainless Steel Characteristics	QVX

How to order

1 2 3 4 5
GN 6341-ST-8-26-B-ZB

1	**Material**
2	**d_1**
3	**d_2**
4	**Type**
5	**Surface**