



Rostfrei
Inox
Stainless
Steel

- 4 Type**
- A** Extension-tapped holes, radial
 - B** Extension-tapped holes, axial

d ₁	d ₂ H10 Bore series		b ±0,2	d ₃	d ₄	l ₁	l ₂	m	k Bore series		s	t	x ≈ Max. protrusion of cap screw	Adjustable hand lever for d ₃
	1	2							1	2				
30	B 12	-	11	M 4	M 3	13	15	8	9,7	-	2,1	4	0,7	GN 311-30-M4-12-SW
32	B 14	-	11	M 4	M 3	14	15,5	8	10,8	-	2,1	4	0,7	GN 311-30-M4-12-SW
36	B 15	B 16	13	M 5	M 4	15	19,9	10	11,7	12	2,1	5,5	1,4	GN 311-30-M5-13-SW
42	B 18	B 20	15	M 5	M 4	17	24,7	12	13,7	14,3	3	5,5	0,6	GN 311-30-M5-15-SW
48	B 22	B 25	15	M 5	M 4	20	26,5	12	16,4	17,2	3	5,5	0	GN 311-45-M5-16-SW
55	B 28	B 30	15	M 6	M 5	22,5	31,6	18	18,7	19,3	3	7	0,5	GN 311-45-M6-18-SW
60	B 32	B 35	15	M 6	M 5	25	33,2	18	21,2	22	4	7	0,4	GN 311-45-M6-19-SW
65	B 40	-	15	M 6	M 5	27,5	34,6	18	24,7	-	4	7	0,5	GN 311-45-M6-20-SW

Specification

- Stainless steel AISI 316LHC Sintered **NI**
- Socket cap screw DIN 912 Stainless steel AISI 304
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 311 → Page 1159
- Damping Washers GN 7062.30 → Page 1161
- Sensor Holders GN 7062.10 → Page 1160

Information

With extension-tapped holes of the semi-split shaft collars GN 7062.1, sensor holders GN 7062.10 or other elements such as the gear lever or cam can be attached to shafts and axles.

They can be assembled safely and easily with a high clamping force by reducing the slot height, without damaging the surface of shafts and axles.

The thread d₃ for sizes d₁ = 30 to 36 is designed as a through hole; for sizes d₁ = 42 and larger, it is designed as blind hole.

see also...

- Semi-Split Shaft Collars GN 7072.1 (with Extension-Tapped Holes) → Page 1155

How to order	1 d ₁
	2 d ₂
GN 7062.1-55-B28-NI-A	3 Material
	4 Type