



<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>			<b>b</b>	<b>d<sub>3</sub></b>	<b>x ≈</b> Max. protrusion of cap screw	Max. recommended tightening torque in Nm
35	B 12	B 14	B 16	13	M 4	1	2
40	B 18	B 20	-	14	M 4	0,75	2
50	B 22	B 25	B 30	14	M 5	2,4	3
65	B 35	B 40	-	14	M 5	0,2	3

**Specification**

- Plastic Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 80 °C
  - Black-gray, matte
- Socket cap screw DIN 912  
Stainless steel AISI 316L
- Hex nut DIN 934  
Stainless steel AISI 316L
- *ISO Fundamental Tolerances* → Page 2151
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS



**Information**

Split shaft collars GN 707.5 can be assembled radially, e.g., on cables, shafts and axles as an end stop. The clamping is done by the slot height, wherein the surface is properly protected by the plastic.

Combined with the stainless steel screws and nuts, the extremely light-weight plastic elements are particularly suitable for use in corrosive environments.

How to order

**GN 707.5-35-B14-SG**

<b>1</b>	<b>d<sub>1</sub></b>
<b>2</b>	<b>d<sub>2</sub></b>
<b>3</b>	<b>Color</b>