




1	2	3												
d ₁	d ₂	Length l							b	d ₃	h ₁	h ₂	r	
		Steel				Stainless steel								
48	M 5	16	20	30	-	-	-	-	7	13,5	24	5,5	20,5	
48	M 6	16	20	25	30	20	30	-	7	13,5	24	5,5	20,5	
48	M 8	-	-	-	-	20	30	40	7	13,5	24	5,5	20,5	
55	M 8	20	30	40	-	20	30	40	8	16	28	6,5	21,5	
55	M 10	20	30	40	-	-	-	-	8	16	28	6,5	21,5	
63	M 8	20	30	40	-	-	-	-	9	19	32	7,5	22,5	
63	M 10	20	30	40	-	20	30	40	9	19	32	7,5	22,5	

Specification

Knob

Plastic, polyamide (PA)

- Glass fiber reinforced
- Black-gray, matte finish similar to RAL 7021

Threaded stud

• Steel

S

Zinc plated, blue passivated

• Stainless steel AISI 303

N

Cover cap

Plastic, polyamide (PA)

Black-gray, RAL 7021, matte finish

Retaining ring / Ball chain

Plastic, polyacetal (POM), black

Key ring on type P

Stainless steel AISI 301, chemically blackened

Operating temperature

0 °C to +60 °C

Wing screws GN 634.13 feature the same premium design and convenient handling as all products of the Ergostyle® family.

The affixed retaining ring allows wing screws GN 634.13 to be secured with a ball chain or retaining cable to prevent loss.

Type P is delivered with attached retaining ring and ball chain.

see also... [ganternorm.com](https://www.ganternorm.com)

- GN 640 Wing Nuts (Small Type)
- GN 834 Wing Nuts
- GN 633 Wing Screws
- GN 634 | GN 635 Wing Nuts (with Loss Protection GN 111.7)

Technical Information

Product Family Ergostyle®

Plastic Characteristics

Stainless Steel Characteristics

Accessory [ganternorm.com](https://www.ganternorm.com)

- GN 111.3 Key Rings (Stainless Steel)
- GN 111 Ball Chains (Brass)
- GN 111.5 Ball Chains (Stainless Steel)
- GN 111.2 Retaining Cables (Stainless Steel)
- GN 111.8 Retaining Cables (Stainless Steel Quality Class 4)
- GN 111.4 Spiral Retaining Cables (Plastic)

How to order

1

d₁

2

d₂

3

Length l

4

Material

5

Type

GN 634.13-55-M8-20-N-P

2.2 Tensioning, Clamping with Knobs

1