


elesa
Original design TTA. / TTB.

Rost frei
Inox
Stainless
Steel

2 Type

- D** With slotted holes
- E** With bores

Application example



d		Tube nominal size DIN EN 10220 / EN 10255
Type D	Type E	
B 42,4	-	1 1/4"
B 48,3	B 48,3	1 1/2"
B 60,3	-	2"

Specification
Support head

- Plastic, polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +100 °C
- Black, matte finish

Clamping set

- Stainless steel AISI 304
- Hex head screws DIN 931
- Hex nuts DIN 934
- Washers DIN 125

RoHS

On request

Type D with square 45 x 45

Technical Information	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Support heads GN 6470.2 are used in combination with boiler or threaded tubes to build transport systems or work tables. They connect the structure, e.g. with conveyor belts or control panels, at a right angle to the tube axis.

see also...

	Page
GN 6470 Support Bases	QVX
GN 6470.1 Cross Connectors	QVX
GN 6470.3 Side Support Heads	QVX

How to order

GN 6470.2-B48,3-E

- 1 d
- 2 Type