



d₁	d₂		d₃	h	t₁ min.	t₂ ±0,5
15	M 6	-	12	25	16	3,5
20	M 8	-	14	31	20	3,5
26	M 8	M 10	17	42	20	5
33	M 10	M 12	20	54	40	8
38	M 12	-	23	68	45	11
41	M 14	M 16	25	87	55	14

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- *Plastic Characteristics* → Page 2158
- RoHS

Information

Domed gear knobs GN 719 are very often used in place of ball knobs DIN 319 on switch levers, gear levers etc. Knobs for such applications are often chosen for ergonomic reasons.

see also...

- *Domed Gear Knobs GN 719.2 (with Thread or Press-On Type)* → Page 62

How to order

GN 719-20-M8

1	d₁
2	d₂