


3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10



**elesa**  
Original design MPG-T / MPG-C



- 1 Type**
- T** Retaining profile trapezoidal
  - R** Retaining profile round

<b>d</b>			<b>h</b>	<b>b<sub>0</sub></b>			<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>
Type R			Type T	GN 6475	GN 6475.1	GN 6475.2		
B 10	B 12	B 14	17	18 / 21	18	20	26	15

**Specification**

**Clamp**

- Plastic, polyamide (PA)
- Operating temperature -30 °C to +100 °C
- Shock resistant
- Black

**Socket cap screws / Nuts**

Stainless steel AISI 304

RoHS

**Technical Information**

	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Side guide clamps GN 6475.3 attach side guides to conveyor sections. This also requires the use of flat steel bars 25x8, connecting elements GN 6473.2 and side guide holders GN 6476, GN 6476.2 or GN 6476.3. Multiple side guides can be attached on top of each other.

The side guide is clamped using the socket cap screws. A screw on the application side is required for mounting on the flat bar.

**see also...**

	Page
<b>GN 6475</b> Side Guides (Guide Contour Flat)	QVX
<b>GN 6475.1</b> Side Guides (Guide Contour Rounded)	QVX
<b>GN 6475.2</b> Side Guides (Guide Contour Flat, Stepped)	QVX
<b>GN 6473.2</b> Connecting Elements	QVX
<b>GN 6476</b> Side Guide Brackets (Rigid, with Contact Edge)	QVX
<b>GN 6476.2</b> Side Guide Brackets (Swiveling, with Contact Edge)	QVX
<b>GN 6476.3</b> Side Guide Brackets (Swiveling)	QVX
<b>GN 990</b> Construction Tubes	QVX

**How to order**

<b>GN 6475.3-R-B10</b>	<b>1</b> Type
	<b>2</b> d (h)