



elesa
Original design SPR-A / SPR-V-A



- 1 Identification no.**
- 1 With hand knob
 - 2 Without hand knob

Application example



d₁			h₁		b	d₂	h₂	h₃	h₄	h₅	l₁	l₂	l₃	m₁	m₂	t₁	t₂
D 12	D 14	D 16	Id. no. 1	Id. no. 2													
D 12	D 14	D 16	203	158	37	11	15	76	60	4	70	50	30	42	79	8	2,5

Specification

Bracket / Receiver

- Plastic, polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +100 °C
- Black, matte finish

Hand knob (identification no. 1)

- Plastic, polyamide (PA)
- Glass fiber reinforced
- Black, matte finish
- Threaded bushing, brass
- Hex head screw, stainless steel AISI 304

Swing bolt / Hex nut / Washer

Stainless steel AISI 304

RoHS

Technical Information

	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Side guide brackets GN 6476.2 fasten side guides or side guide segments to conveyor sections. This also requires the use of connecting elements GN 6473.2, retaining profiles GN 6473.1 or side guide clamps GN 6475.3, GN 6475.4 or GN 6475.5.

The stop edge facilitates horizontal alignment on the conveyor system. The swiveling receiver also allows side guides to be mounted that are not perpendicular to the mounting surface of the bracket. Clamping is carried out without tools.

see also...

	Page
GN 6471 Side Guides (Cylinder and Ball Rollers on One Side)	QVX
GN 6472 Side Guides (Cylinder and Ball Rollers on Two Side)	QVX
GN 6473 Side Guide Segments (Cylinder and Ball Rollers on One Side for Curves)	QVX

How to order

	1 Identification no.
GN 6476.2-2-D14-158	2 d ₁
	3 h ₁