
**3 Type**

- N** Neutral  
**M** With arrow  
**S** With scale 0...9, 20 graduations

**1****2**

<b>d<sub>1</sub></b>	<b>d<sub>2</sub> H8</b>		<b>d<sub>3</sub> -0,2</b>	<b>d<sub>4</sub></b>	<b>d<sub>5</sub></b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>l<sub>3</sub></b>	<b>l<sub>4</sub></b>	<b>t<sub>1</sub> min.</b>	<b>t<sub>2</sub></b>
27	B 6	-	33,5	23,5	M 4	25,5	7,5	10,5	12,5	23,5	7,5
34	B 6	B 8	41	29,5	M 5	29,5	9,5	13,5	13	26,5	9,5
42	B 8	B 10	50	37,5	M 5	33,5	10,5	15,5	15	30,5	11,5

**Specification****Knob**

Aluminum

- Anodized, natural color
- Arrow for type M laser-engraved
- Scale for type S laser-engraved

**Grub screw DIN 916**

Stainless steel

with internal hex and with serrated point

RoHS

**On request**

- Special graduations (see „How to Order Graduations“)

Control knobs GN 723.4 can be combined with reference flanges GN 723.3 which offer the following advantages:

- they are provided with a reference mark relating to the scale on the control knobs
- they give additional support to the control shaft
- the version with a friction ring prevents unexpected movement through vibration.

Scale and arrow on the control knobs are indelibly marked and easily legible. Besides the standard scale (type S) they can be supplied with any type of graduation.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to Order Graduations“.

see also...

Page

GN 726.2 Control Knobs (Aluminium)

QVX

**Technical Information**

How to order - Graduations

QVX

ISO Fundamental Tolerances

QVX

**Accessory**

GN 723.3 Reference Flanges

QVX

GN 826 Clamping Elements (for Adjustable Spindles)

QVX

How to order

GN 723.4-42-B10-S

<b>1</b>	<b>d<sub>1</sub></b>
<b>2</b>	<b>d<sub>2</sub></b>
<b>3</b>	<b>Type</b>



Control knob GN 723.4 combined with a reference flange GN 723.3 → Page XYZ

