



1 d ₁	2 d ₂	3 l ₁ ±1	b	h	l ₂	l ₃	l ₄	t min.	
30	M 6	M 8	400	22	90	440	360	480	15
30	M 6	M 8	500	22	94	540	460	580	15
30	M 6	M 8	600	22	98	640	560	680	15

Specification

Handle tube

Wall thickness 1,5 mm

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Handle legs / Covers, black, matte finish ● **EL**
 - Anodized, natural color ● **ES**
 - Handle legs / Covers, black, matte finish ● **ES**
 - Anodized, natural color ● **ES**
 - Handle legs silver / Covers, light gray, matte finish
- Stainless steel AISI 304
 - Ground, matte shiny finish ● **NG**
 - Handle legs / Covers, black, matte finish

Handle legs

- Aluminum
- Powder coated, textured finish
- Black, RAL 9005 for SW / EL / NG
- Silver, RAL 9006 for ES
- Threaded bushing
- Steel, zinc plated

Covers

- Plastic, thermoplastic elastomer (TPE)
- Black, matte finish for SW / EL / NG
- Light-gray, matte finish for ES

RoHS

With their curved type, GN 666.4 tubular arch handles highlight modern machine design.

The production method used allows special solutions to be realised, e. g. with other radii of curvature or other leg heights.

see also...

	Page
GN 666 Tubular Handles (Mounting from the Back)	QVX

Technical Information

Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

1 d ₁
2 d ₂
3 l ₁
4 Finish

GN 666.4-30-M6-500-EL

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

