

ROSTFREI
Inox
Stainless
Steel

Inch
sizes
available

4 Type

- K** With plastic cover cap
- E** With stainless steel cover cap

1 d_1	2 d_2 GN 666.5	2 d_3 GN 666.7	3 $l_1 \pm 0,5$	$l_2 \pm 0,3$ Threaded bore for mounting stud of GN 666.7	d_4	h	l_3	l_4	t min.	
30	M 6	M 8	M 8	200	200	20	60	265	15	15
30	M 6	M 8	M 8	250	250	20	60	315	15	15
30	M 6	M 8	M 8	300	300	20	60	365	15	15
30	M 6	M 8	M 8	400	400	20	60	465	15	15
30	M 6	M 8	M 8	500	500	20	60	565	15	15
30	M 6	M 8	M 8	600	600	20	60	665	15	15

Specification

- Tube \varnothing 30 x 1,5
Stainless steel AISI 304
Matte shiny finish, ground
- Handle legs
Stainless steel AISI 304
Matte shiny finish, ground
- Mounting stud (GN 666.7)
With threaded pin DIN 913-M8
Stainless steel AISI 304
- Grub screw DIN 914-M5
Stainless steel AISI 304
- Covers
 - Type K
Plastic (Polyamide PA), black matte
 - Type E
Stainless steel AISI 304
- [Load Rating Information](#) → Page 2106
- [Stainless Steel Characteristics](#) → Page 2166
- **RoHS**
- **On request**
 - Special lengths

Information

For a mounting of stainless steel tubular handles GN 666.7 (mounting from operator's side) the stud is first screwed in from the machine side with the threaded pin DIN 913-M8x25 (included) and then the handle is pushed on and secured with the grub screw DIN 914-M5.

Type E of stainless steel tubular handles GN 666.5 and GN 666.7 is completely made of A2 stainless steel.

see also...

- [Stainless Steel Cabinet U-Handles GN 426.5](#) → Page 155
- [Stainless Steel Tubular Handles GN 333.7](#) → Page 181

How to order (Mounting from the back)


GN 666.5-30-M6-600-E

1	d_1
2	d_2
3	l_1
4	Type

How to order (Mounting from operator's side)

GN 666.7-30-M8-400-K

1	d_1
2	d_3
3	l_1
4	Type




1.1

1.2

1.3

1.4



2.1

2.2

2.3

2.4

Example of application

Tubular handles GN 666.5 / GN 666.7 allow the mounting of a pair of handles in opposite position. This method could be used on doors (double handle).

Generally a modification of the thread length l_4 is required for this. The included threaded pin DIN 913-M8x25-A2 of the mounting stud needs to be replaced by a longer threaded pin, too.

Handles with a modified thread length l_4 are available on request.

