



elesa
Original design M.343-SOFT



3 Type

- A Mounting from the back (threaded blind bore)
- B Mounting from the operator's side

1	2	2										
$l_1 \pm 0,5$	d_1 Type A	d_2 Type B	a	b	d_3	h_1	h_2	l_2	l_3	t_1 min.	t_2	
132	M 6	6,4	16	26	10,5	53	15	148	116	12	8,5	
132	M 8	-	16	26	-	53	15	148	116	12	8,5	

Specification

Base body

- Plastic, polypropylene (PP)
- Black-gray, matte finish, similar to RAL 7021
- Bushings brass

Insert with finger recesses

- Plastic, thermoplastic elastomer (TPE)
- Chemically bonded to the base body
- Operating temperature 0 °C to +80 °C
- Color

- Orange, RAL 2004, matte finish ● OR
- Gray, RAL 7024, matte finish ● GR
- Red, RAL 3000, matte finish ● RT
- Green, RAL 6017, matte finish ● GN

RoHS

Cabinet U-handles GN 725.3 are characterized by their stability and their ergonomic design. The soft finger recesses (Softline product family) on the underside of the handle provide a particularly pleasant feel when gripping.

Cabinet U-handles GN 725.3 can be installed from the rear (type A) as well as from the operating side (type B).

see also...

	Page
GN 328 Cabinet U-Handles (Aluminum)	QVX
GN 528 Cabinet U-Handles (Plastic)	QVX
GN 628 Cabinet U-Handles (Plastic)	QVX
GN 565.1 Cabinet U-Handles (Aluminum)	QVX

Technical Information

Product Family Softline	QVX
Strength Properties	QVX
Plastic Characteristics	QVX

How to order

1	l_1
2	d_1 (d_2)
3	Type
4	Insert color

GN 725.3-132-M8-A-RT