



elesa

Original design EBK.SOFT



1	2	3				d₃	h₁	h₂
d₁	d₂	Length l						
43	M 6	16	20	25	-	32,5	55	17,5
43	M 8	16	20	25	30	32,5	55	17,5
43	M 10	20	25	30	50	32,5	55	17,5
50	M 8	16	20	25	30	37	64	20
50	M 10	20	25	30	50	37	64	20

Specification

Base body

Plastic, Polypropylen (PP)

Softline coating

Elastomer (TPE) 70 Shore A

- Chemically bonded with base body
- FDA compliant plastic granulate
- Operating temperature 0 °C to +80 °C
- Black, matte finish

Threaded stud

Steel

Zinc plated, blue passivated

RoHS

On request

Retaining ball handles

The design of the ball handles with threaded stud GN 675 matches the product family Ergostyle®. The Softline coating makes the control knobs particularly user-friendly and ergonomic.

The **soft, slip-proof** contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures.

The Softline ball handles are suitable for use both as operating elements and for clamping. The „hard“ plastic core guarantees the perfect anchoring engagement of the threaded bushing, also under heavier loads.

see also...

	Page
GN 675 Ball Handles (Internal Thread, without Cover Cap)	QVX
GN 675.1 Ball Handles (Internal Thread, with Cover Cap)	QVX

Technical Information

Product Family Ergostyle®	QVX
Product Family Softline	QVX
Plastic Characteristics	QVX

How to order

GN 675-50-M10-25

1	d₁
2	d₂
3	Length l