

3 Type

A With arrow
B Neutral, without indicator point or scale
S With scale 0...9, 20 graduations

4 Identification no.

1 With grub screw
2 With collet

1	2		2										
d_1	d_2 H8 Bore		d_3 Collet	d_4	d_5	d_6	d_7	h_1	h_2	h_3	h_4	Length l	t
22	B 5	-	-	16	14	M 4	20	22	16	4,3	8	12,5	-
27	B 6	-	Z 6	20	18	M 4	25	26	20	4,3	9	14	14
34	B 6	B 8	Z 8	25	23	M 5	32	30	24	4,2	10	15	17
42	B 8	B 10	Z 10	32	30	M 5	40	34	28	4	11	16	20

Specification

Knob
Aluminum
- Anodized, black
- Arrow for type A
  White, laser-engraved
- Scale for type S
  White, laser-engraved

Cover
Plastic, light gray

Collet / Hex nut
Brass

Grub screw DIN 916
Stainless steel
with internal hex and serrated point

RoHS

On request

- Special graduations
  (see „How to Order Graduations“)

The light gray cover of the control knobs GN 726.1 shrouds the fixing components as well as the shaft ends. The cover also lends itself for a logo or other symbols.
The collet version permits a simple adjustment of the types with scale or arrow.
Scale and arrow on the control knobs are indelibly marked and easily legible since the engraved „aluminum colored“ numbers contrast with the black anodized surface.
Besides the standard scale (type S) the control knobs can be supplied with any type of graduation.
Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to Order Graduations“.

see also...	Page
GN 626 Control Knobs (Plastic)	QVX
GN 726.2 Control Knobs (Aluminium, with Scale Ring)	QVX

Technical Information

How to Order Graduations	QVX
ISO Fundamental Tolerances	QVX

Accessory

GN 826 Clamping Elements (for Adjustable Spindles)	QVX

How to order

1 2 3 4
GN 726.1-42-B10-A-1

1	d_1
2	d_2 (d_3)
3	Type
4	Identification no.