



elesa

Original design EKK-SST-SAN



Inox  
Stainless  
Steel



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
21	M 5	12,5	18	10,5	10
31	M 8	18,5	27	17	15

**Specification**

**Knob**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black-gray, RAL 7021, matte finish
- White, RAL 9016, matte finish



**WSA**

**Threaded bushing**

Stainless steel AISI 303

RoHS

Knurled knobs GN 676 are manufactured from an antimicrobial plastic. Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilising at temperatures below 130 °C will also have no effect on the antimicrobial property.

With these properties, the handles are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...	Page
GN 676 Knurled Knobs	QVX
GN 676.1 Knobs (Steel, Blackened)	QVX
GN 676.2 Knobs (Steel, Zinc Plated)	QVX
GN 676.5 Knobs (Stainless Steel)	QVX
GN 76 Mushroom Shaped Knobs (Phenolic Resin)	QVX

**Technical Information**

Product Family Sanline	QVX
Product Family Ergostyle®	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

**How to order**

**GN 676-31-M8-SGA**

<sup>1</sup> d <sub>1</sub>
<sup>2</sup> d <sub>2</sub>
<sup>3</sup> Finish