



- 3 Type**
- A** With arrow
  - B** Neutral, without indicator point or scale
  - S** With scale 0...9  
20 graduations
- 4 Identification no.**
- 1** With grub screw
  - 2** With collet

<b>1</b> $d_1$	<b>2</b> $d_2$ H8 Bore		<b>2</b> $d_3$ Collet	$d_4$	$d_5$	$d_6$	$d_7$	$h_1$	$h_2$	$h_3$	$h_4$	$l$	$t$
22	B 5	-	-	16	14	M 4	20	22	16	4,3	8	12,5	-
27	B 6	-	Z 6	20	18	M 4	25	26	20	4,3	9	14	14
34	B 6	B 8	Z 8	25	23	M 5	32	30	24	4,2	10	15	17
42	B 8	B 10	Z 10	32	30	M 5	40	34	28	4	11	16	20

**Specification**

- Aluminum  
Black anodized
- Scale (Type S) and arrow (Type A)  
White, engraved with laser precision
- Cover  
Plastic, light gray
- Collet / Hexagon nut  
Brass
- Stainless steel grub screw DIN 916  
with internal hexagon and serrated point
- ISO Fundamental Tolerances → Page 2151
- RoHS

**On request**

- Special graduations  
see „How to Order Graduations“  
→ Page 326

**Information**

The light gray cover of the control knobs GN 726.1 shrouds the fixing components as well as the shaft end. The cover also lends itself for a logo or other symbols.

The collet version permits a simple adjustment of the types with scale or arrow.

Scale and arrow on the control knobs are indelibly marked and easily legible since the engraved „aluminum colored“ numbers contrast with the black anodized surface.

Besides the standard scale (Type S) the control knobs can be supplied with any type of graduation.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to Order Graduations“ → Page 326.

see also...

- Control Knobs GN 723.4 (Aluminum) → Page 340
- Clamping Elements GN 826 (for Adjustable Spindles) → Page 346

<p><b>How to order</b></p> <p><b>GN 726.1-42-B10-A-1</b></p>	<b>1</b>	$d_1$
	<b>2</b>	$d_2$ ( $d_3$ )
	<b>3</b>	Type
	<b>4</b>	Identification no.