



**2 Type**

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side



$l_1 \pm 0,25$ GN 728	$l_1 \pm 0,25$ GN 728.5	b	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>	s	t <sub>1</sub> min.	t <sub>2</sub>
120	120	22,5	M 6	6,4	11	42,5	6,5	147	108	8	10	6,5
180	-	27	M 8	8,4	13,5	47,5	7,5	214	165	10	12	8,5

**Specification**

- **GN 728**  
Aluminum die casting
  - Powder coated
    - Black, RAL 9005, textured finish ● **SW**
    - Silver, RAL 9006, textured finish ● **SR**
  - Plain, tumbled ○ **BL**
- **GN 728.5**  
Stainless steel AISI CF-8
  - Precision casting
  - Matte shot-blasted
- *Load Rating Information* → Page 2106
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**



**Information**

The installation of cabinet U-handles GN 728 / GN 728.5 can be carried out from the back (Type A) as well as from the operator's side (Type B).

see also...

- *Product Family Standard Parts for Profile Systems* → Page 18
- *Cabinet U-Handles GN 528 (Plastic, Mounting from the Operator's Side)* → Page 120
- *Cabinet U-handles GN 528.1 (Plastic, Mounting from the Back)* → Page 121
- *Assembly Sets for Profile Systems 30 / 40 GN 965* → Page 2086
- *Assembly Sets for Profile Systems 30 / 40 / 45 GN 968* → Page 2096

How to order (Aluminum)

**GN 728-120-A-SW**

- 1  $l_1$
- 2 Type
- 3 Finish

How to order (Stainless steel)

**GN 728.5-120-B**

- 1  $l_1$
- 2 Type