


4 Type

- MS** Brass pivot
- KU** Plastic pivot, Polyacetal (POM)
- ZK** Spherical pivot

Mounting example



1	2	3					d₃	d₄	d₅	d₆ +0,05	h₁	h₂	l₂	l₃	l₄ ≈
34	M 6	15	20	25	30	16	4	3,5	4,5	21	10,5	1	1,3	5,1	
42	M 8	20	25	30	40	19	6	5	6,1	26	13	1,5	1,6	6,2	
53	M 10	25	30	40	50	24	8	6,5	7,8	32	16	2	1,9	7,3	

Specification

Knob

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Threaded stud

Stainless steel AISI 304

Cover cap

Plastic, Polyamide (PA)
Light gray, matte finish

RoHS

Accessory

	Page
GN 631 Thrust Pads (Plastic)	QVX
GN 631.2 Thrust Pads (NBR)	QVX
GN 631.5 Thrust Pads (Stainless Steel)	QVX

Knurled screws GN 7336.5, type MS/KU with brass or plastic pivots are used when pressure dents or damage must be avoided.

Knurled screws GN 7336.5, type ZK feature a spherical pivot whose Ø d₆ is smaller than the core Ø of the thread. The version with spherical pivot is suitable for holding thrust pads GN 631 / GN 631.2 / GN 631.5, which must be ordered separately.

The knurled screws GN 7336.5 distinguish an attractive design in combination with closed shape (no recess on the underside of the handles).

see also...

	Page
GN 6336.10 Star Knobs (with Pivot)	QVX
GN 6336.12 Star Knobs (with Movable Thrust Pad)	QVX
GN 421.10 Knurled Screws (with Pivot)	QVX
GN 421.12 Knurled Screws (with Movable Thrust Pad)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

1	d₁
2	d₂
3	l₁
4	Type

GN 7336.5-42-M8-25-MS

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

