



* recommended diameter tolerance

d₁	d₂ H10		b ±0,2	d₃	d₄	l₁	l₂	s
16*	B 4	B 5	9	M 3	10,5	26,5	22	2,1
20	B 6	-	9	M 3	10,5	29,5	22	2,1
22	B 8	-	9	M 3	10,5	29,5	22	2,1
26	B 10	-	11	M 4	10,5	37	30	2,1
30	B 12	-	11	M 4	13	31	22	2,1
32	B 14	-	11	M 4	13	37	30	2,1
36	B 15	B 16	13	M 5	13	38,5	30	2,1
42	B 18	B 20	15	M 5	13	41	30	3
48	B 22	B 25	15	M 5	13	43	45	3
55	B 28	B 30	15	M 6	13	45	45	3
60	B 32	B 35	15	M 6	13	46,5	45	4
65	B 40	-	15	M 6	13	47,5	45	4

* This size is only available in steel and stainless steel.

Specification

Shaft Collar

- Steel
- Sintered
- Black oxidized with vapor
- Aluminum
- Turned, tumbled
- Stainless steel AISI 316L
- Sintered

3

ST

AL

NI

Adjustable hand lever

- Zinc die casting
- Powder coated
- Black RAL 9005, textured finish
- Insert / Retaining screw
- Stainless steel AISI 303

RoHS

Semi-split shaft collars GN 706.4 can safely and simply be clamped by reducing the slot height by using an adjustable hand lever and thus they act, for instance, like an end stop.

This version offers great advantages especially for applications that demand new positions of the shaft collar.

The thread d_3 for sizes $d_1 = 32$ and 36 is designed as a through hole; for sizes $d_1 = 42$ and larger, it is designed as blind hole.

see also...

GN 706.2 Semi-Split Shaft Collars (with Socket Cap Screw)	Page QVX
--	--------------------

Technical Information

List of Shaft Collar Types	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 7062.30 Damping Washers	QVX
-----------------------------------	-----

How to order

GN 706.4-36-B16-AL

1	d₁
2	d₂
3	Material

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

