



**2 Identification no.**

- 1 Without vent hole
- 2 With vent hole

**GN 745.2**



1

1

<b>d<sub>1</sub></b>					<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>e ≈</b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>s</b>
<b>GN 745</b>				<b>GN 745.2</b>	Vent hole					
G 1/8	M 10 x 1,5	M 12 x 1,5	-	-	2	15	22	9	16	19
G 1/4	M 14 x 1,5	-	-	G 1/4	2	15	22	9	17	19
G 3/8	M 16 x 1,5	-	-	G 3/8	2	17,5	25,5	9	18	22
G 1/2	M 18 x 1,5	M 20 x 1,5	-	G 1/2	2	21	32	11	20	27
G 3/4	M 22 x 1,5	M 25 x 1,5	M 26 x 1,5	G 3/4	2	25	37	12	22	32
G 1	M 35 x 1,5	-	-	G 1	2	31	44	13	23	38
G 1 1/4	M 40 x 1,5	-	-	G 1 1/4	2	38	53,5	14	26	46
G 1 1/2	-	-	-	G 1 1/2	2	46	63,5	15	28	55

**Specification**

- Plastic (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 100 °C
  - Black, matte finish

- Seal
  - Rubber NBR (Perbunan®)

- O-ring
  - Rubber NBR (Perbunan®)

• *Elastomer Characteristics* → Page 2158

• *Plastic Characteristics* → Page 2158

• RoHS

**Accessory**



**GN 745.1**  
neutral



**GN 747.1**  
with re-fill  
symbol



**GN 740.1**  
with drain  
symbol

**Information**

Suitable for threaded plugs GN 745 are self-adhesive, matt anodized aluminum disks (0.3 mm thick) which can be supplied in sizes  $d_3 = 15$  to 31.

see also...

- *Plugs GN 740 (Red, with DIN-Drain Symbol)* → Page 1586
- *Plugs GN 747 (with DIN-Re-Fill Symbol)* → Page 1587
- *Plugs GN 741 / GN 742 (Aluminum)* → Page 1590

How to order (With flat sealing ring)

**GN 745-G<sup>1</sup>/<sub>4</sub>-1**

1 **d<sub>1</sub>**

2 **Identification no.**

How to order (With O-ring)

**GN 745.2-G<sup>1</sup>/<sub>2</sub>-1**

1 **d<sub>1</sub>**

2 **Identification no.**

How to order (Aluminum disk)

**GN 740.1-25**

3 **d<sub>3</sub>**