



- 3 Type
- A Mounting with countersunk screw

1 r	2 d ₁	b	d ₂	d ₃	l ₁	l ₂	l ₃	l ₄	Load F max. in N
45	M 6	13	19	9	12	13	8,5	0,5	500
65	M 8	18	25	14	14	16	10,5	0,6	1000

Specification

Latch

- Zinc die casting
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

- SW
- SR

Indexing mechanism

Stainless steel

Countersunk screw DIN 7991

Stainless steel

RoHS

Stop locks GN 720 may be used as stops and feature a high degree of stability.

The inside ball-spring latching mechanism has 4 latching positions at a distance of 90° each. Thanks to the bolt attachment using the countersunk screw, the latching position is freely selectable.

The bar is solid and may be machined, if required.

The countersunk screw is enclosed part of the order.

How to order		1 r
1	2	d ₁
3	Type	
4	Color	

GN 720-65-M8-A-SW