



d_1	d_2	d_3	$l_1 \approx$	l_2	l_3	$l_4 \approx$	l_5	l_6
16	M 5	16	58	15	5	52,5	9,5	5
18	M 5	16	72,5	15	5	67	9,5	5
22	M 6	20	80,5	19,5	6	74	10,5	7
24	M 6	20	95,5	19,5	6	89	10,5	7
25	M 6	20	105,5	19,5	6	98,5	10,5	7

Specification

Handle
Plastic, Polyamide (PA)
• Operating temperature up to 90 °C
• Black, matte finish
• Revolving

KT

Typical in design are the retractable handles GN 798.3 / GN 798.5 with their stepped shape consisting of two cylinders giving the operator a better grip, especially when pulling the handle out from its locked position before it can be folded back into the rest position.

Retractable handles GN 798.3 / GN 798.5 are used when the handle should not protrude temporarily for space or safety reasons.

GN 798.3

Retractable mechanism

Steel, blackened

GN 798.5

Retractable mechanism

Stainless steel

- Spindle, AISI 303
- Flat base, AISI 316LHC, sintered

RoHS

see also...

	Page
GN 598.3 Retractable Handles (Retractable Mechanism Steel, Locked in Operating Position)	QVX
GN 598.5 Retractable Handles (Retractable Mechanism Stainless Steel, Locked in Operating Position)	QVX

Technical Information

	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Steel)	1	Material
GN 798.3-KT-22	2	d_1

How to order (Stainless Steel)	1	Material
GN 798.5-KT-25	2	d_1