


- 3 Type**
- A** For indexing plungers / cam action indexing plungers with chamfered pin top / bottom
  - B** For indexing plungers / cam action indexing plungers with chamfered pin right / left



<b>1</b>	<b>2</b>	<b>b<sub>1</sub></b>	<b>s</b>	<b>b<sub>2</sub> +0,3</b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>h<sub>3</sub></b>	<b>k<sub>1</sub></b>	<b>k<sub>2</sub></b>	<b>k<sub>3</sub></b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>m</b>	<b>A/F</b>	<b>t</b>
		13	20	6,5	10	7,5	1,5	19	2,5	1,5	48	26,5	34	10	11
		20	30	10	15	14	5	27,5	3	2	80	40	55	17	17

Specification

Precision steel casting

- Zinc plated, blue passivated
- Zinc plated and powder coated
- Black, RAL 9005, textured finish

**ZB**

**SW**

Precision stainless steel casting AISI CF-8

**NI**

RoHS

Technical Information

Page

Overview of Indexing Plungers	QVX
Overview of Cam Action Indexing Plungers	QVX
Stainless Steel Characteristics	QVX

Catches GN 724.10 are combined with spring latches and indexing plungers of series GN 724 ff. when the application requires multiple indexing positions or catches. The orientation of the chamfered pin according to the combination options shown on the standard sheet must be taken into account when selecting the catch.

The slotted holes with hex enable fastening with socket cap screws ISO 4762, hex head screws DIN 931 or hex nuts DIN 934.

see also...

	Page
<b>GN 724.1</b> Spring Latches (for Welding)	QVX
<b>GN 724.2</b> Spring Latches (with Flange for Surface Mounting)	QVX
<b>GN 724.3</b> Spring Latches (with Flange for Surface Mounting)	QVX
<b>GN 724.4</b> Indexing Plungers (for Welding)	QVX
<b>GN 724.5</b> Indexing Plungers (with Flange for Surface Mounting)	QVX
<b>GN 724.6</b> Indexing Plungers (with Flange for Surface Mounting)	QVX

How to order

<b>1</b>	<b>b<sub>1</sub></b>
<b>2</b>	<b>s</b>
<b>3</b>	<b>Type</b>
<b>4</b>	<b>Finish (Material)</b>

**GN 724.10-13-20-A-ZB**