



elesa
Original design M.643 / M.643 HT

1 2

Length l	d						a	b	h	t min.				
	Standard material (PP)			HT material (PA)						M4	M5	M6	M8	M10
86 ±0,5	M 5	M 6	-	-	M 6	-	14	23	44	-	10	12	-	-
94 ±0,5	M 5	M 6	-	-	-	-	14	24	48	-	10	12	-	-
117 ±0,5	M 4	M 5	M 6	M 8	M 6	M 8	15	25	49	10	10	12	13	-
120 ±0,5	M 5	M 6	M 8	-	-	-	15	25	49	-	10	12	13	-
132 ±0,5	M 5	M 6	M 8	-	-	-	16	26	54	-	10	12	13	-
150 ±1	M 6	M 8	M 10	-	-	-	16	27	56	-	-	12	13	17
160 ±1	M 6	M 8	M 10	-	-	-	16	27	55	-	-	12	13	17
179 ±1	M 8	M 10	-	-	M 8	-	16	27	57	-	-	-	13	17
235 ±1	M 8	M 10	-	-	-	-	18,5	29	61	-	-	-	13	17
300 ±1	M 10	-	-	-	-	-	22	32	64	-	-	-	-	17

Specification

Handle

- Plastic, Polypropylene (PP) —
- Shock resistant
- Operating temperature -20 °C to +100 °C
- Black, matte finish
- Plastic, (Polyamide (PA) HT
- Glass fiber reinforced
- Operating temperature -30 °C to +200 °C
- Black-gray, matte finish

Threaded bushing

Brass

RoHS

Cabinet U-handles GN 725 have a very ergonomic elliptical profile.

see also...

	Page
GN 565 Cabinet U-Handles (Aluminum)	QVX
GN 625 Cabinet U-Handles (Polyamide)	QVX
GN 525 Cabinet U-Handles (Phenolic Resin)	QVX

Technical Information

Strength Properties	QVX
Plastic Characteristics	QVX

How to order (-20 °C to +100 °C)

1	Length l
2	d

GN 725-179-M8

How to order (+30 °C to +200 °C)

1	Length l
2	d
3	Material

GN 725-86-M6-HT