



- 3 Type**
- N Cover plain
  - M Cover with indicator point
- 4 Identification no.**
- 1 With grub screw
  - 2 With collet

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> H8 Bore		<b>2</b> d <sub>3</sub> Collet	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	Length l	t
22	B 5	-	-	16	14	M 4	15	9	4,3	5	-
27	B 6	-	Z 6	20	18	M 4	17	11	4,3	5,5	14
34	B 6	B 8	Z 8	25	23	M 5	20	14	4,2	7	17
42	B 8	B 10	Z 10	32	30	M 5	23	17	4	8,5	20

**Specification**

- Knob**  
Aluminum  
Anodized, black
- Hub cover**  
Plastic, light gray
- Collet / Hex nut**  
Brass
- Grub screw DIN 916**  
Stainless steel  
with internal hex and serrated point
- RoHS

The light gray cover of the control knobs GN 726 shrouds the fixing components as well as the shaft end. The cover also lends itself for a logo or other symbols.

Made from an aluminum extrusion allows the manufacture of customized solutions in existing diameters at relatively low cost.

see also...

	Page
GN 726.1 Control Knobs (Aluminium)	QVX
GN 526 Control Knobs (Plastic, with Steel Bushing)	QVX
GN 626 Control Knobs (Plastic)	QVX

**Technical Information**

ISO Fundamental Tolerances	QVX
----------------------------	-----

**Accessory**

GN 826 Clamping Elements (for Adjustable Spindles)	QVX
--	-----

How to order

**GN 726-34-Z8-M-2**

<b>1</b>	d <sub>1</sub>
<b>2</b>	d <sub>3</sub> (d <sub>2</sub> )
<b>3</b>	Type
<b>4</b>	Identification no.

