




elesa

Original design EGH-SOFT



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Bore	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> min.
22	B 8	18	85	60

### Specification

#### Base body

Plastic, Polypropylen (PP)

#### Softline coating

Thermoplastic elastomer (TPE)

- Chemically bonded with base body
- FDA compliant material
- Operating temperature 0 °C to +80 °C
- Black, matte finish
- Hardness 70 Shore A

RoHS

The handle GN 819 does not require a thread at the shaft.

During mounting, easy blows with a soft hammer are sufficient to drive the handle into place, the shaft end should be slightly rounded or chamfered (30°). The handle sits absolute vibration-tight.

The softline coating makes the handle particularly user-friendly and ergonomic.

#### Technical Information

	Page
Product Family Ergostyle®	QVX
Product Family Softline	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order

**GN 819-22-B8**

<sup>1</sup> d<sub>1</sub>

<sup>2</sup> d<sub>2</sub>