



- 3 Type**
- N Cover plain
 - M Cover with indicator point
- 4 Identification no.**
- 1 With grub screw
 - 2 With collet

1 d ₁	2 d ₂ H8 Bore		2 d ₃ Collet	d ₄	d ₅	d ₆	h ₁	h ₂	h ₃	Length l	t
22	B 5	-	-	16	14	M 4	15	9	4,3	5	-
27	B 6	-	Z 6	20	18	M 4	17	11	4,3	5,5	14
34	B 6	B 8	Z 8	25	23	M 5	20	14	4,2	7	17
42	B 8	B 10	Z 10	32	30	M 5	23	17	4	8,5	20

Specification

Knob

Aluminum
Anodized, black

Hub cover

Plastic, light gray

Collet / Hex nut

Brass

Grub screw DIN 916

Stainless steel
with internal hex and serrated point

RoHS

The light gray cover of the control knobs GN 726 shrouds the fixing components as well as the shaft ends. The cover also lends itself for a logo or other symbols.

Made from an aluminum extrusion allows the manufacture of customized solutions in existing diameters at relatively low cost.

see also...	Page
GN 726.1 Control Knobs (Aluminium)	QVX
GN 526 Control Knobs (Plastic, with Steel Bushing)	QVX
GN 626 Control Knobs (Plastic)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
----------------------------	-----

Accessory

GN 826 Clamping Elements (for Adjustable Spindles)	QVX
--	-----

How to order

GN 726-34-Z8-M-2

1	d ₁
2	d ₃ (d ₂)
3	Type
4	Identification no.