



**2 Type**

- A** Mounting hole parallel to the spindle axle
- B** Mounting hole vertical to the spindle axle
- S1** Mounting with hex head screw

**3 Coding**

- SR** With scale 0,1...0,9, 50 graduations ascending clockwise
- SL** With scale 0,1...0,9, 50 graduations ascending anti-clockwise

**1**

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	d <sub>7</sub>	d <sub>8</sub> -0,05 Spigot	d <sub>9</sub>	b <sub>1</sub>	b <sub>2</sub>	h	k <sub>1</sub>	k <sub>2</sub>	l <sub>1</sub> +0,2	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	A/F	w Adjustable range
27	M 6	M 12 x 1	6,4	18	4,3	38	19	12,5	10	20	4,3	28	22	54	19,5	37,5	0,5	1	22	10
34	M 8	M 16 x 1	8,5	23	5,3	50	24	18,3	11	25	4,2	36	30	67	23,5	45,5	0,5	1	27	15

**Specification**

- Body**  
Steel
- Matte chrome plated
- Scales laser-engraved
- Spindle**  
Steel  
Plain
- Control knob**  
Aluminum  
Anodized, black
- Hex head screw**  
Steel  
Zinc plated, blue passivated

- Cover**  
Plastic  
light gray
- RoHS

Control knobs with adjustable spindle GN 727 allow precise adjustment or aligning i. e. of a positive stop. The spindle thread is without backlash. The graduations on the control knob are non-abrasive and well legible. The light gray cover shrouds the fixing components as well as the shaft end. Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale rings on the order sheet „How to Order Graduations“.

Technical Information	Page
Complementary dimensions with technical details	QVX
How to order - Graduations	QVX

How to order	
<b>1</b> d <sub>1</sub>	
<b>2</b> Type	
<b>3</b> Coding	

**GN 727-27-A-SR**



**Control knobs with adjustable spindle GN 727 - Complementary dimensions with technical details**

