



elesa
Original design MPE

l_1	h_1	h_2	h_3	h_4	l_2	l_3	l_4	$m_1 \pm 0,1$	m_2
90	29	16,5	63	20	135	74	41	80	8

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +100 °C
- Color
 - Black, RAL 9005, matte finish
 - Gray, RAL 7035, matte finish
 - White, RAL 9002, matte finish

- SW
- GR
- WS

Pin

Stainless steel AISI 303

Return springs

Stainless steel AISI 302

RoHS

Folding handles GN 825.1 are used in places where the handle must not protrude. After releasing the handle, it returns to its starting position by spring-loaded return.

see also...

	Page
GN 425.2 Folding Handles (Steel / Stainless Steel, in Both End Positions Retained)	QVX
GN 425.5 Folding Handles (Steel / Stainless Steel, in Both End Positions Retained)	QVX
GN 825.2 Folding Handles with Recessed Tray (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Strength Properties	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 825.1-90-SW

1 l_1

2 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

