Control Handwheels

Plastic, Hub Bushing Brass



elesa
ELESA original design MBT+I

iF product design award

3 Type

D With revolving knob

1 d_1	2 d_2 H9	d_3	d_4	d_5	b	l_1	l_2	l_3	l_4	r
40	B 6	17	M 4	13,5	14	26,5	14	20	4	12,5
50	B 6	20	M 5	13,5	17	33	18	20	5	16,5
60	B 8	23	M 5	16	20,5	39	20	23	6	20,5
70	B 10	24	M 5	16	21,5	42	25	23	6	25
85	B 10	29	M 5	16	20	30,5	22	23	6	32,5
100	B 10	35	M 5	16	20	31	22	23	6	40

Specification

4

Wheel body
Plastic, Polypropylene (PP)
- Reinforced, shock-resistant
- Operating temperature 0 °C to +90 °C
- Black, matte finish

Cover cap
Plastic, Polyamide (PA)

• Black, RAL 9005, matte finish	–
• Orange, RAL 2004, matte finish	DOR
• Gray, RAL 7035, matte finish	DGR
• Yellow, RAL 1021, matte finish	DGB
• Blue, RAL 5024, matte finish	DBL
• Red, RAL 3000, matte finish	DRT
• Green, RAL 6017, matte finish	DGN

Hub bushing
Brass

Grub screw DIN 916
Stainless steel
With internal hex and serrated point

Revolving knob GN 595
Plastic, Polyamide (PA)
- Black, matte finish
- Spindle steel
  Zinc plated, blue passivated

RoHS

Control handwheels GN 735 are used for setting operations with low torque. Coarse setting is made by means of the cylindrical handle (fingertip grip) followed by fine setting using the knurled rim of the handwheel.

see also...	Page
GN 736 Control Handwheels (Aluminum, Anodized Black)	QVX
GN 736.1 Control Handwheels (Aluminum, Anodized Black, with Scale Lug)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

Accessory

GN 826 Clamping Elements (for Adjustable Spindles)	QVX

How to order
1 2 3
GN 735-40-B6-D

1	d_1
2	d_2
3	Type

How to order
1 2 3 4
GN 735-60-B8-D-DRT

1	d_1
2	d_2
3	Type
4	Color of the cover cap