



| d <sub>1</sub> |            |            |            |                |                  |                  |                |                |                |                |                |    |  |
|----------------|------------|------------|------------|----------------|------------------|------------------|----------------|----------------|----------------|----------------|----------------|----|--|
| GN 740         |            | GN 740.2   |            | d <sub>2</sub> | e <sub>1</sub> ≈ | e <sub>2</sub> ≈ | l <sub>1</sub> | l <sub>2</sub> | l <sub>3</sub> | s <sub>1</sub> | s <sub>2</sub> |    |  |
| G 1/8          | M 10 x 1,5 | M 12 x 1,5 | -          | -              | 15               | 21,5             | -              | 9              | 16             | 19             | 19             | -  |  |
| G 1/4          | M 14 x 1,5 | -          | -          | G 1/4          | 15               | 21,5             | 22             | 9              | 16             | 19             | 19             | 19 |  |
| G 3/8          | M 16 x 1,5 | -          | -          | G 3/8          | 17               | 25               | 25,5           | 9              | 16             | 22             | 22             | 22 |  |
| G 1/2          | M 18 x 1,5 | M 20 x 1,5 | -          | G 1/2          | 20,5             | 29,5             | 32             | 11             | 18             | 26             | 26             | 27 |  |
| G 3/4          | M 22 x 1,5 | M 25 x 1,5 | M 26 x 1,5 | G 3/4          | 25               | 36,5             | 37             | 12             | 20             | 32             | 32             | 32 |  |
| G 1            | M 35 x 1,5 | -          | -          | G 1            | 31               | 44               | 44             | 13             | 22             | 38             | 38             | 38 |  |
| G 1 1/4        | M 40 x 1,5 | -          | -          | G 1 1/4        | 38               | 52,5             | 53,5           | 14             | 24             | 46             | 46             | 46 |  |
| G 1 1/2        | -          | -          | -          | G 1 1/2        | 46               | 63               | 63,5           | 15             | 26             | 55             | 55             | 55 |  |

**Specification**

- Plastic Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 100 °C
  - Red
- Seal Rubber NBR (Perbunan®)
- O-ring Rubber NBR (Perbunan®)
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- RoHS

**Information**

Threaded plugs GN 740 / GN 740.2 are generally supplied as drain plugs in red color.

see also...

- *Threaded Plugs GN 745 (without Symbol)* → Page 1584
- *Threaded Plugs GN 741 / GN 742 (Aluminum)* → Page 1590

How to order (With overlying seal)

**GN 740-G<sup>3</sup>/<sub>4</sub>**

1 d<sub>1</sub>

How to order (With collared O-ring)

**GN 740.2-G<sup>1</sup>/<sub>2</sub>**

1 d<sub>1</sub>